

# TRYON OTG

## ULTRA-COVER

TRYON is now available in a Premium over-the-glasses version. It has PLATINUM® coating, maximum cover and extendable temples for a precise fit. TRYON OTG can be worn with most prescription glasses.

 PLATINUM



  
40g



TRYOTGPSI • Clear





TRYOTGPSF • Smoke

- + FLEXIBLE UPPER FOREHEAD PROTECTION (TPR)
- +  PLATINUM COATING (  )
- + PC/TPR ADJUSTABLE AND STRETCHABLE CO-INJECTED TEMPLES
- + 160° FLEX TEMPLES

**bolle**  
SAFETY

# TRYON OTG

## ULTRA-COVER

MODEL	VERSIONS	REFERENCES	LENS MARKING	FRAME MARKING	COATINGS
TRYON OTG	 Clear	TRYOTGPSI	IO	AS/NZS 1337.1.2010	Anti-scratch/Anti-fog/Platinum
	 Smoke	TRYOTGPSF	I3	AS/NZS 1337.1.2010	Anti-scratch/Anti-fog/Platinum

### LENS MARKING

**P**. Platinum is a permanent coating applied on both sides of the lens that gives a high resistance to scratching (1.4 cd / m<sup>2</sup>) and to the most aggressive chemicals and delays the onset of fogging for two minutes, as per the testing requirements of EN166.

- I**. The letter 'I' signifies 'Medium Impact' approval.
- O**. The letter 'O' signifies that the product has been approved for the use both outdoors and indoors, and the terminology used by Australian standards is 'outdoor un-tinted'. This marking appears on all clear, amber and contrast lenses.

### Ocular lens category:

- O**. Range of luminous transmittance 80–100% (Clear).
- 3**. Range of luminous transmittance 8–18% (Smoke).

### TECHNOLOGIES

#### PLATINUM

The new exclusive scratch and fog resistant coating K and N certified PLATINUM® guarantees even more safety, reliability and comfort. Washable (water and soap), this permanent coating applied on both sides of the lens makes it highly scratch resistant and effectively delays the appearance of fogging.

### LENS

- 2 mm polycarbonate
- Platinum coating on both sides of Clear & Smoke
- 100% UV385: Clear
- 100% UV400: Smoke

### FRAME MARKING

**AS/NZS 1337.1.2010:** Tested and approved to AS/NZS 1337.1.2010 for Medium Impact protection

### CLEANING AND STORAGE

**CLEANING:** The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system.

**MAINTENANCE:** Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfiber pouch or rigid case.

**STORAGE:** All products must be stored in a dry and clean environment.

CHARACTERISTICS	
LENSES	PC – 2,2 mm – Curve 4
FRAME	-
TEMPLES	PC + TPR
UPPER PROTECTION	TPR
SPARE LENSES	No

21/05/2018

#### ASIA/PACIFIC HEADQUARTERS:

Bollé Australia Pty Ltd  
32–40 Fairchild Street  
Heatherton VIC 3202  
T: 1300 138 098  
E: safety@bolle.com.au

[bollesafety.com.au](http://bollesafety.com.au)

#### NEW ZEALAND:

T.: 0800 2655 369  
E: bolle@bolle.co.nz

**bolle**  
SAFETY